

Intelligent control LED integrated light source

### **Features and Benefits**

- Intelligent reverse connect protection, the power supply reverse connection does not damage the IC.
- The control circuit and the LED share the only power source.
- Control circuit and RGB chip are integrated in a package of 5050 components, form a complete control of pixel point.
- Built-in signal reshaping circuit, after wave reshaping to the next driver, ensure wave-form distortion not accumulate.
- Built-in electric reset circuit and power lost reset circuit.
- Each pixel of the three primary color can achieve 256 brightness display, completed 16777216 color full color display, and scan frequency not less than 400Hz/s.
- Cascading port transmission signal by single line.
- Any two point the distance more than 5m transmission signal without any increase circuit.
- When the refresh rate is 30fps, cascade number are not less than 1024 points.
- Send data at speeds of 800Kbps.
- The color of the light were highly consistent, cost-effective..

### **Applications**

- Full-color module, Full color soft lights a lamp strip.
- LED decorative lighting, Indoor/outdoor LED video irregular screen.

### **General description**

WS2812B is a intelligent control LED light source that the control circuit and RGB chip are integrated in a package of 5050 components. It internal include intelligent digital port data latch and signal reshaping ampli fication drive circuit. Also include a precision internal oscillator and a 12V voltage programmable constant curr e-nt control part, effectively ensuring the pixel point light color height consistent.


The data transfer protocol use single NZR communication mode. After the pixel power-on reset, the DIN port receive data from controller, the first pixel collect initial 24bit data then sent to the internal data latch, the other data which reshaping by the internal signal reshaping amplification circuit sent to the next cascade pixel through the DO port. After transmission for each pixel, the signal to reduce 24bit, pixel adopt auto resharping transmit technology, making the pixel cascade number is not limited the signal transmission, only depend on the speed of signal transmission.


LED with low driving voltage, environmental protection and energy saving, high brightness, scattering angle is large, good consistency, low power, long life and other advantages. The control chip integrated in LED above becoming more simple circuit, small volume, convenient installation.




Intelligent control LED integrated light source


### **Mechanical Dimensions**







### PIN configuration



### **PIN** function

NO.	Symbol	Function description
1	VDD	Power supply LED
2	DOUT	Control data signal output
3	VSS	Ground
4	DIN	Control data signal input

### **Absolute Maximum Ratings**

Prameter	Symbol	Ratings	Unit
Power supply voltage	$V_{ m DD}$	+3.5~+5.3	V
Input voltage	V <sub>I</sub>	-0.5∼VDD+0.5	V
Operation junction temperature	Topt	-25~+80	$^{\circ}$
Storage temperature range	Tstg	-55~+150	${\mathbb C}$

Electrical Characteristics ( $T_A$ =-20 $\sim$ +70 $^{\circ}$ C,  $V_{DD}$ =4.5 $\sim$ 5.5 $V_{SS}$ =0 $V_{S$ 



Intelligent control LED integrated light source

Prameter	Smybol	conditions	Min	Тру	Max	Unit
Input current	$I_{\rm I}$	$V_I = V_{DD}/V_{SS}$			±1	μА
Innut valta as laval	V <sub>IH</sub>	D <sub>IN</sub> , SET	$0.7V_{\mathrm{DD}}$			V
Input voltage level	V <sub>IL</sub>	D <sub>IN</sub> , SET			$0.3~\mathrm{V}_\mathrm{DD}$	V
Hysteresis voltage	$V_{\mathrm{H}}$	D <sub>IN</sub> , SET		0.35		V

## Switching characteristics ( $T_A$ =-20 $\sim$ +70 $^{\circ}$ C, $V_{DD}$ =4.5 $\sim$ 5.5V, $V_{SS}$ =0V,unless otherwise specified)

Prameter	Symbol	Condition	Min	Тру	Max	Unit
Operation frequency	Fosc2			800		KHz
Transmission delay time	$t_{ m PLZ}$	CL=15pF,DIN $\rightarrow$ DOUT,RL=10K $\Omega$			300	ns
Fall time	$t_{ m THZ}$	CL=300pF,OUTR/OU TG/OUTB			120	μs
Data transmission rate	$F_{MAX}$	Duty ratio50%	400			Kbps
Input capcity	$C_{I}$				15	pF



Intelligent control LED integrated light source


### LED characteristic parameter

Emitting color	Model	Wavelength(nm)	Luminous intensity(mcd)	Voltage(V)
Red	13CBAUP	620-630	550-700	1.8-2.2
Green	13CGAUP	515-530	1100-1400	3.0-3.2
Blue	10R1MUX	465-475	200-400	3.0-3.4


### Data transfer time( TH+TL=1.25µs±150ns)

ТОН	0 code ,high voltage time	0.35us	±150ns
T1H	1 code ,high voltage time	0.9us	±150ns
TOL	0 code, low voltage time	0.9us	±150ns
T1L	1 code ,low voltage time	0.35us	±150ns
RES	low voltage time	Above 50μs	

### **Sequence chart:**



### **Cascade method:**




http://www.world-semi.com



Intelligent control LED integrated light source

### Data transmission method:



Note: The data of D1 is send by MCU, and D2, D3, D4 through pixel internal reshaping amplification to transmit.

### Composition of 24bit data:

																						'	
G7	G6	G5	GA	G3	G2	G1	GO	R7	R6	R5	R4	R3	R2	R1	R0	B7	B6	l B5	B4	B3	B2	B1	B0
U/	UU	U.	G4	G3	G2	GI	GU	IX/	IXO	I IXJ	17.4	IC.5	11.2	11.1	IXU	ן ט	DU	100	דען	100	102	ונטן	ן טען
																					1 '	( '	i .
				l .	l											l	l .			l .	1 '	í	

Note: Follow the order of GRB to sent data and the high bit sent at first.



Intelligent control LED integrated light source

## **Typical application circuit:**

